



WARNING! Usage of safety mats and safety mat devices is governed by each user's local codes and applicable industry standards. Improper usage of these devices could result in severe injuries. In the event that Larco safety mats do not prevent all access to the hazardous operation, the unprotected access must be guarded by other appropriate safeguarding devices or barriers. The Zone Monitor 3000 Safety Mat Control Unit offers a sophisticated mix of advanced mat system monitoring and simple dependability.

Designed for the toughest industrial environments, the Zone Monitor 3000 provides individual mat status indicators for up to four Larco safety mats through high-visibility LEDs. In addition, the Zone Monitor 3000 can accommodate a variety of power requirements and is designed to meet or exceed CE, UL and CUL safety system requirements.

# Features & Benefits

### • **Combines Sophistication and Simplicity** The first control of its kind to offer the dependability of field-proven, reliable technology, while providing the user with diagnostic outputs

needed to maintain productivity and reduce downtime

#### Advanced Individual Mat Diagnostics

Offers the unique ability to indicate open circuits on individual mats to make diagnostics easy

#### Rugged Design

Suitable for tough industrial environments with an enclosure rated IP 65 and NEMA 12

#### • Flexible Power Inputs and Operation Modes

Accommodates a variety of power requirements, including 120 VAC, 240 VAC and 24 VDC and offers two modes of operation (automatic restart and guard only) in one unit

#### • Dependable and Long Lasting

Field replaceable relay pack designed to last more than 500,000 electrical cycles at 1 Amp.

• Designed to Meet UL, CE, and CUL Requirements Designed to meet or exceed ANSI B11.19-2003, UL 508-1999,

EN 1760-1-1998. Designed to meet Category 3 safety requirements.

![](_page_0_Picture_18.jpeg)

1902 13th Street SE • PO Box 547 • Brainerd, MN 56401 phone 218-829-9797 • toll free phone 800-523-6996 fax 218-829-0139 • toll free fax 800-589-3705

www.larcomfg.com

# **Controller Specifications**

Response Time	<30 milliseconds	Electrical Fast Transients (EFT)	+/-1kV (power supply) +/-0.5kV (control signals)
Indicators	Run = Green LED Stop = Red LED Mat Status = 4 Mat Activated Red LEDs 4 Mat Disconnected Yellow LEDs Relay Fault = Internal Yellow LED	Restart Function	Selectable manual or automatic restart Internal/Lockout restart and External/ Remote restart available
Operational Modes	Selectable automatic restart and guard only modes	Reset Function	Power-up and Relay Fault Reset internal manual push-button
Power Input	120 VAC (for 60Hz), 240 VAC (for 50 Hz) or 24 VDC	Enclosure	Steel (Powdercoat Machinery Black) 8" h x 6" w x 3.75" d (203 mm x 152 mm x 95 mm)
Rated Supply Current	0.125A AC, 0.75 A DC	Enclosure Rating	NEMA 12, IP 65
Cafaby Innuts	Commentations for up to four 1	Mounting	Surface Mount
Salety inputs	wire safety mats with up to 40' cord length each (quick disconnect mat connections	Shipping Wt.	11 lbs.
	also available)	Operating Temperature	32° F to 122° F (0° C to 50° C)
Safety Output Relays	Two captive contact relays with two closed when run (NO) and one open when run (NC) sets of contacts rated 8 amps at 230 VAC	Relative Humidity	Acceptable Range = 20-90%
		Standards of	Designed to meet UL 508-1999 Standard for
Replaceable Relay Pack Life	Mechanical: 10,000,000 operations Electrical: 500,000 operations at 1 amp at 240 VAC	Conformity	Industrial Control Equipment, ANSI B11.19- 2003 Performance Criteria for Safeguarding, OSHA 1910.212-1996 General Machine Guarding, ANSI/RIA 15.06-
Electrostatic Discharge (ESD)	+/-10kV (air discharge) +/-6kV (contact discharge)		1999 Industrial Robots and Robots Systems-Safety Requirements, EN/IEC
Radiated RF Field	10 volts/meter, 100 to 1,000 MHz		and EN 1760-1998 Safety of Machinery, Pressure Sensitive Protective Devices

# **Details & Dimensions**

![](_page_1_Figure_3.jpeg)

![](_page_1_Figure_4.jpeg)

![](_page_1_Figure_5.jpeg)

![](_page_1_Picture_6.jpeg)

www.larcomfg.com